



- NOTES:
1. ALL PARTS TO BE BULK PACKED.
  2. CONTACTS ASSEMBLED INTO CONNECTOR.
  3. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE. DIMENSIONS IN BRACKETS [ ] ARE METRIC.
  4. PC TAIL LENGTH OPTIONS:
    - STANDARD (SHORT) TAIL = 0.114in [W4281-1XPG-300]
    - INTERMEDIATE = 0.202in [W4291-1XPG-300]
    - LONG = 0.257in [W4292-1XPG-300]

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4291-10PG-300	10 - #20	11, 12
W4291-11PG-300	11 - #20	12
W4291-12PG-300	12 - #20	NONE
W4291-1XPG-300		


NO. OF CONTACTS




FACE VIEW  
W4291-10PG-300  
10-POS.



FACE VIEW  
W4291-11PG-300  
11-POS.




FACE VIEW  
W4291-12PG-300  
12-POS.



HEX NUT  
MAT'L: UV THERMOPLASTIC,  
BLACK

O-RING  
MAT'L: RUBBER,  
BLACK


13/16-27 UNS-2A  
MOD. THREAD





PIN CONTACT  
PC TAIL  
GOLD PLATED

PANEL INSERT, PIN  
MAT'L: UV THERMOPLASTIC,  
BLACK


.188 MAX.  
[4.8mm]  
PANEL THICKNESS



PC TAIL VIEW  
W4291-10PG-300 - 10-POS. (11&12 CLOSED)  
W4291-11PG-300 - 11-POS. (12 CLOSED)  
W4291-12PG-300 - 12-POS. (ALL OPEN)



PC TAIL LAYOUT





RECOMMENDED  
PANEL CUTOUT  
STANDARD MULTI-CON-X

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_

DATE: \_\_\_\_\_

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1		
REV.	INIT.	DATE	DESCRIPTION		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY:	DATE:	 601 E. WILDWOOD VILLA PARK, IL 60181
			PAK	10/24/14	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			CHECKED BY:		
			APPROVED BY:		
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			TITLE:		
			PANEL PIN, E-KEY 12-POS., #20 PC TAIL, INTERMEDIATE MULTI-CON-X, WEATHER RESISTANT		
			CUSTOMER: STANDARD PRODUCT		
	= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX		SCALE	SIZE	SHEET
			NTS	B	1 OF 1
FILE: W4291-1XPG-300			DIRECTORY:	PART NUMBER:	
			SLW	W4291-1XPG-300	REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[W4291-12PG-300](#) [W4291-11PG-300](#) [W4291-10PG-300](#)