


CUSTOMER PRINT

PART NUMBER: W4292-1XSG-300


- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS ASSEMBLED INTO CONNECTOR.
 3. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.
 4. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.105in [W4281-1XSG-300]
 - INTERMEDIATE = 0.202in [W4291-1XSG-300]
 - LONG = 0.267in [W4292-1XSG-300]

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4292-10SG-300	10 - #20	11, 12
W4292-11SG-300	11 - #20	12
W4292-12SG-300	12 - #20	NONE
W4292-1XSG-300		


NO. OF CONTACTS




MATING VIEW
W4292-10SG-300
10-POS.



MATING VIEW
W4292-11SG-300
11-POS.



MATING VIEW
W4292-12SG-300
12-POS.



HEX NUT
MAT'L: UV THERMOPLASTIC,
BLACK

O-RING
MAT'L: RUBBER,
BLACK


13/16-27 UNS-2A
MOD. THREAD

.267 REF.
[6.8mm]
SEE NOTE 4

SOCKET CONTACT
PC TAIL, LONG
GOLD PLATED



PANEL INSERT, SOCKET
MAT'L: UV THERMOPLASTIC,
BLACK

.188 MAX.
[4.8mm]
PANEL THICKNESS




PC TAIL VIEW

W4292-10SG-300 - 10-POS. (11&12 CLOSED)
W4292-11SG-300 - 11-POS. (12 CLOSED)
W4292-12SG-300 - 12-POS. (ALL OPEN)



PC TAIL LAYOUT




**RECOMMENDED
PANEL CUTOUT**
STANDARD MULTI-CON-X

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1			
REV.	INIT.	DATE	DESCRIPTION			
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: DATE:		 601 E. WILDWOOD VILLA PARK, IL 60181	
			PAK 10/22/14			
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			CHECKED BY:		APPROVED BY: TITLE: PANEL SOCKET, E-KEY 12-POS. #20 PC TAIL, LONG MULTI-CON-X, WEATHER RESISTANT STANDARD PRODUCT	
▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE	SIZE	SHEET	CUSTOMER:
			NTS	B	1 OF 1	
			FILE:	DIRECTORY:	PART NUMBER:	REV
			W4292-1XSG-300	SLW	W4292-1XSG-300	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[W4292-10SG-300](#) [W4292-12SG-300](#) [W4292-11SG-300](#)