



MFG. ENG.	APPROVED BY:	DATE:	QA	APPROVED BY:	DATE:
--------------	--------------	-------	----	--------------	-------

NOTES:


- ALL PARTS TO BE BULK PACKED UNLESS NOTED.
- INSTA CLICK PANEL MOUNT ASSEMBLY IS SUPPLIED WITH CONTACTS INSERTED INTO THE CONNECTOR. ACCEPTS WIRE 12, 14 AND 16 AWG.
- ALL DIMENSIONS ARE REFERENCED IN INCHES [MM], WITHIN ± 0.015 UNLESS NOTED.



FACE VIEW
W4181-3SG-P-300
3 #12 CONTACT STYLE IS SHOWN



HEX NUT
MATL: UV THERMOPLASTIC, BLACK



WASHER GASKET
MATL: RUBBER, BLACK

PANEL MOUNT, SOCKET
MATL: UV THERMOPLASTIC, BLACK


W 4 X 8 X - X SG - P - 3 XX

CONTACT SIZES
1' - SIZE #12
2' - SIZE #20
3' - SIZE #16


CONTACTS STYLE
0' - CRIMP
1' - SOLDER
2' - PC TAIL

ES - EPOXY FILLED
00 - NO EPOXY


CONTACTS POSITIONS
POSTION 2, 3 & 4 (AVAILABLE IN SIZE #12)
POSITION 4, 5 & 6 (AVAILABLE IN SIZE #16)
POSOTION 4,5,6,7,8,9,10,11&12 (AVAILABLE IN SIZE #20)




PC TAILS SHOWN HERE
CRIMP AND SOLDER VERSIONS AVAILABLE
REFER TO PART NUMBER SYSTEM




WIRE VIEW
W4181-3SG-P-300
3 #12 CONTACT STYLE IS SHOWN




WIRE VIEW
W4281-9SG-P-300




WIRE VIEW
W4281-8SG-P-300




WIRE VIEW
W4281-7SG-P-300




WIRE VIEW
W4281-6SG-P-300




WIRE VIEW
W4281-5SG-P-300




WIRE VIEW
W4281-4SG-P-300




WIRE VIEW
W4381-6SG-P-300




WIRE VIEW
W4381-5SG-P-300




WIRE VIEW
W4381-4SG-P-300




WIRE VIEW
W4182-4SG-P-300



WIRE VIEW
W4182-3SG-P-300



WIRE VIEW
W4182-2SG-P-300



SIDE VIEW SHOWN
W4182-3SG-P-300

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

0A	AM	03/03/22	CUSTOMER DRAWING	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: AM	DATE: 03/03/22
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			CHECKED BY:	
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS $\pm .005$ ANGLES $\pm 1^\circ$ FRACTIONS $\pm 1/16$			APPROVED BY:	
$\triangleright$ - CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE: NTS	SIZE: B
			SHEET: 1 OF 1	TITLE: PANEL CONNECTOR ASSEMBLY (2-4) #12, (4-6) #16, (4-12) #20 SOCKET CONTACTS MULTI CONX INSTA-CLICK STANDARD PRODUCT
			FILE: FILE NAME	DIRECTORY: SLW
			PART NUMBER: W4X8X-XSG-P-3XX	REV 0A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[W4181-2SG-P-300](#) [W4181-3SG-P-300](#) [W4182-2SG-P-300](#) [W4182-3SG-P-300](#) [W4281-12SG-P-300](#) [W4281-9SG-P-300](#) [W4282-12SG-P-300](#) [W4282-9SG-P-300](#) [W4381-4SG-P-300](#) [W4382-4SG-P-300](#) [W4281-10PG-P-3ES](#) [W4282-10PG-P-300](#) [W4280-11SG-P-300](#) [W4281-11SG-P-3ES](#) [W4281-6SG-P-3ES](#) [W4280-10PG-P-300](#) [W4282-7PG-P-3ES](#) [W4281-8PG-P-3ES](#) [W4182-4PG-P-3ES](#) [W4282-10PG-P-3ES](#) [W4281-11PG-P-300](#) [W4282-10SG-P-300](#) [W4282-12SG-P-3ES](#) [W4281-10SG-P-300](#) [W4280-4PG-P-3ES](#) [W4281-9SG-P-3ES](#) [W4282-8SG-P-3ES](#) [W4282-5PG-P-318](#) [W4281-12SG-P-3ES](#) [W4280-6SG-P-535](#) [W4282-11SG-P-3ES](#) [W4280-12SG-P-300](#) [W4282-9SG-P-3ES](#) [W4281-8SG-P-3ES](#) [W4280-11PG-P-300](#) [W4282-5SG-P-3ES](#) [W4281-5SG-P-3ES](#) [W4281-6PG-P-3ES](#) [W4282-9PG-P-3ES](#) [W4282-5PG-P-3ES](#) [W4281-10SG-P-3ES](#) [W4281-5PG-P-3ES](#) [W4280-12PG-P-300](#) [W4282-10SG-P-3ES](#) [W4281-7PG-P-3ES](#) [W4282-8PG-P-3ES](#) [W4280-6SG-P-530](#) [W4282-6PG-P-3ES](#) [W4181-2SG-P-3ES](#) [W4282-12PG-P-3ES](#) [W4181-3SG-P-3ES](#) [W4281-12PG-P-3ES](#) [W4282-11PG-P-3ES](#) [W4281-10PG-P-300](#) [W4281-11SG-P-300](#) [W4182-2SG-P-3ES](#) [W4282-11PG-P-300](#) [W4182-3SG-P-3ES](#) [W4282-6SG-P-3ES](#) [W4281-7SG-P-3ES](#) [W4282-11SG-P-300](#) [W4281-9PG-P-3ES](#) [W4281-11PG-P-3ES](#) [W4282-7SG-P-3ES](#) [W4280-10SG-P-300](#)