


- NOTES:
- 1. ALL PARTS TO BE BULK PACKED.
 - 2. CONTACTS ARE SUPPLIED UNASSEMBLED
 - 3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE
 - 4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

ASS'Y P/N	GROMMET SIZE
W6280-XPG-P-513	.148 GROMMET I.D. FOR CABLE O.D. 0.13 - 0.15 [3.3 - 3.8]
W6280-XPG-P-516	.176 GROMMET I.D. FOR CABLE O.D. 0.16 - 0.18 [4.1 - 4.6]
W6280-XPG-P-519	.206 GROMMET I.D. FOR CABLE O.D. 0.19 - 0.21 [4.8 - 5.3]
W6280-XPG-P-522	.245 GROMMET I.D. FOR CABLE O.D. 0.22 - 0.25 [5.6 - 6.3]
W6280-XPG-P-526	.265 GROMMET I.D. FOR CABLE O.D. 0.25 - 0.27 [6.3 - 6.8]
W6280-XPG-P-528	.280 GROMMET I.D. FOR CABLE O.D. 0.26 - 0.28 [6.6 - 7.1]


ASSEMBLY P/N	CONTACTS
W6280-2PG-P-5XX	2 #20
W6280-3PG-P-5XX	3 #20
W6280-4PG-P-5XX	4 #20
W6280-5PG-P-5XX	5 #20
W6280-6PG-P-5XX	6 #20
W6280-XPG-P-5XX	

GROMMET SIZE


NUMBER OF CONTACTS




MATING FACE
W6280-2PG-P-5XX SHOWN



SHOWN ASSEMBLED
W6280-2PG-P-5XX SHOWN




CONTACT
HEIGHT
SEE NOTE 2



CABLE-END HOUSING
MAT'L: UV PBT, BLACK
COUPLING RING
MAT'L: UV PBT, BLACK
O-RING
MAT'L: SILICONE, RED
SPRING
MAT'L: STAINLESS STEEL


(2-6) #20 PIN CONTACT, CRIMP
MAT'L: COPPER ALLOY, GOLD PLATED




GROMMET
MAT'L: SANTOPRENE, BLACK

.190
[4.8]


CABLE GRIP
MAT'L: POLYPROPYLENE, BLACK




BACKSHELL
MAT'L: UV PBT, BLACK




WIRING END
W6280-2PG-P-5XX SHOWN
WITHOUT HARDWARE




WIRING END
W6280-2PG-P-5XX




WIRING END
W6280-3PG-P-5XX



WIRING END
W6280-4PG-P-5XX



WIRING END
W6280-5PG-P-5XX



WIRING END
W6280-6PG-P-5XX

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

B	MA	02-24-21	ADDED W6280-XPG-P-526 TO CHART PER ECR 9544
A	MA	02-28-20	RELEASED PER PDR 16014-7
	PNK	01-15-18	PDR 16014
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK DATE: 01-15-18
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16 = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			CHECKED BY:
APPROVED BY:			APPROVED BY:
SCALE NTS	SIZE B	SHEET 1 OF 1	TITLE: CABLE-END ASSEMBLY 2-6 #20 PIN CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X STANDARD PRODUCT
FILE: W6280-XPG-P-5XX	DIRECTORY: SLW	PART NUMBER: W6280-XPG-P-5XX	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[W6280-2PG-P-528](#) [W6280-5PG-P-528](#) [W6280-3PG-P-528](#) [W6280-6PG-P-528](#) [W6280-4PG-P-528](#)