


NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.

CONNECTOR P/N	POSITIONS		CONTACT STYLE	CABLE O.D. RANGE
	#16	#20		
W6C80-6SG-513	2	4	CRIMP	0.13-0.15" (3.3 -3.8 mm)
W6C80-6SG-516			CRIMP	0.16-0.18" (4.1 -4.6 mm)
W6C80-6SG-519			CRIMP	0.19-0.21" (4.8 -5.3 mm)
W6C80-6SG-522			CRIMP	0.22-0.25" (5.6 -6.3 mm)
W6C80-6SG-528			CRIMP	0.26-0.285" (6.6 -7.2 mm)
W6C82-6SG-513			SOLDER	0.13-0.15" (3.3 -3.8 mm)
W6C82-6SG-516			SOLDER	0.16-0.18" (4.1 -4.6 mm)
W6C82-6SG-519			SOLDER	0.19-0.21" (4.8 -5.3 mm)
W6C82-6SG-522			SOLDER	0.22-0.25" (5.6 -6.3 mm)
W6C82-6SG-528			SOLDER	0.26-0.285" (6.6 -7.2 mm)
NOTE: ADD SUFFIX "W" TO ANY CONNECTOR P/N ABOVE FOR WINGED COUPLING RING OPTION				



0A	PNK	01-19-16	PDR 14001 PRELIMINARY		
REV.	INIT.	DATE	DESCRIPTION		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF CONXALL CORPORATION. UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK	DATE: 01-19-16	 601 E. WILDWOOD VILLA PARK, IL 60181
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			CHECKED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:		TITLE: CABLE-END CONNECTOR 2-16 + 4-20 SOCKET CONTACTS MINI-CON-X POWER/SIGNAL CUSTOMER: STANDARD PRODUCT
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE: NTS	SIZE: B	
FILE: W6C8X-6SG-5XX_CD			DIRECTORY: SLW	SHEET: 1 OF 1	PART NUMBER: W6C8X-6SG-5XX_CD
REV 0A					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[W6C82-6SG-528](#)