







- NOTES:
- 1. SOLDER CUP SOCKET CONTACTS ARE INSTALLED (SHOWN)
 - 2. ALL DIMENSIONS ARE FOR REFERENCE.


ASS'Y P/N	EPOXY
W7882-10SG-300	NO
W7882-10SG-3ES	YES



FACE VIEW
7882-10SG-300 SHOWN



ASSEMBLED VIEW
FOR CUSTOMER REFERENCE



RECOMMENDED
PANEL CUT-OUT
TOLERANCE: ±.003

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

RoHS COMPLIANT

CUSTOMER DRAWING

0A	AM	04/05/16	FIRST DRAWN
REV.	INIT.	DATE	DESCRIPTION
AM		04/05/16	
CHECKED BY:			
APPROVED BY:			
SCALE	SIZE	SHEET	TITLE
NTS	B	1 OF 1	PANEL CONNECTOR ASSEMBLY (10) #22 SOCKET CONTACT, SOLDER MINI-CON-X
FILE:	DIRECTORY:	PART NUMBER:	CUSTOMER: STANDARD PRODUCT
	SLW	W7882-10SG-3XX	
			REV 0A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[W7882-10SG-3ES](#) [W7882-10SG-300](#)