




- NOTES:
1. CRIMP CONTACTS SUPPLIED UNASSEMBLED AND WITHOUT EPOXY BACKING.
 2. HEX-NUT TORQUE: 8-10 IN-LB.
 3. DIMENSIONS ARE REFERENCE ONLY, IN INCHES [mm], WITHIN ±0.015 UNLESS OTHERWISE NOTED.




MATING FACE
W7882-10PG-P-300 SHOWN




RECOMMENDED PANEL CUTOUT



W7882-8PG-P-300




W7882-9PG-P-300




W7882-10PG-P-300


CONTACT ARRANGEMENTS (WIRING END SHOWN)



CRIMP CONTACTS (SHOWN ASSEMBLED)
W7880-10PG-P-300 SHOWN



SOLDER CONTACTS
W7882-10PG-P-300 SHOWN



PC TAIL CONTACTS
W7883-10PG-P-3ES SHOWN


PANEL-MOUNT CONNECTOR PART NUMBERS:

W 7 8 8 X - X P G - P - 3XX


CONTACTS STYLE:
0 = CRIMP
2 = SOLDER
3 = PC TAIL

OF CONTACTS:
8-10 #22 PINS

EPOXY BACKING:
3ES = WITH EPOXY
300 = WITHOUT EPOXY



WIRING END
W7882-10PG-P-300 SHOWN




WIRING END
W7882-10PG-P-300 SHOWN

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

0A		PNK		03-15-18		PDR16014											
REV.		INIT.		DATE		DESCRIPTION											
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.						ORIG. DRAWN BY: PNK			DATE: 03-15-18			 601 E. WILDWOOD VILLA PARK, IL 60181					
						CHECKED BY:											
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.						APPROVED BY:						TITLE: PANEL-MOUNT CONNECTOR 8-10 #22 PIN CONTACTS INSTA-CLICK™ MINI-CON-X CUSTOMER: STANDARD PRODUCT					
						SCALE NTS		SIZE B		SHEET 1 OF 1							
▽ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX						FILE: W788X-XPG-P-3XX_CD			DIRECTORY: SLW			PART NUMBER: W788X-XPG-P-3XX			REV 0A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[W7882-9PG-P-300](#) [W7881-9PG-P-300](#) [W7881-9PG-P-3ES](#) [W7880-9PG-P-300](#) [W7882-9PG-P-3ES](#)