

PART NUMBER: W8C8X-6SG-5XX CD

CONNECTOR P/N	POSITIONS		CONTACT STYLE	CABLE O.D. RANGE
	#16	#20		
W8C80-6SG-513	2	4	CRIMP	0.13-0.15" (3.3 -3.8 mm)
W8C80-6SG-516			CRIMP	0.16-0.18" (4.1 -4.6 mm)
W8C80-6SG-519			CRIMP	0.19-0.21" (4.8 -5.3 mm)
W8C80-6SG-522			CRIMP	0.22-0.25" (5.6 -6.3 mm)
W8C80-6SG-528			CRIMP	0.26-0.285" (6.6 -7.2 mm)
W8C82-6SG-513			SOLDER	0.13-0.15" (3.3 -3.8 mm)
W8C82-6SG-516			SOLDER	0.16-0.18" (4.1 -4.6 mm)
W8C82-6SG-519			SOLDER	0.19-0.21" (4.8 -5.3 mm)
W8C82-6SG-522			SOLDER	0.22-0.25" (5.6 -6.3 mm)
W8C82-6SG-528			SOLDER	0.26-0.285" (6.6 -7.2 mm)



0A		PNK		01-19-16		PDR 14001 PRELIMINARY																	
REV.		INIT.		DATE		DESCRIPTION																	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.						ORIG. DRAWN BY: PNK			DATE: 01-19-16			CONXALL 601 E. WILDWOOD VILLA PARK, IL 60181											
						CHECKED BY:																	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 ▽ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX						APPROVED BY:			TITLE: CABLE-TO-CABLE CONNECTOR 2-16 + 4-20 SOCKET CONTACTS MINI-CON-X POWER/SIGNAL														
						SCALE NTS			SIZE B			SHEET 1 OF 1			CUSTOMER: STANDARD PRODUCT								
						FILE: W8C8X-6SG-5XX_CD			DIRECTORY: SLW			PART NUMBER: W8C8X-6SG-5XX_CD											
															REV 0A								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[W8C82-6SG-519](#)