

NOTES:

1. 0.126 [3,2] MAX. PANEL THICKNESS.

2. MATERIALS:

BODY - BRASS, NICKEL OR GOLD PLATED
 TIP TERMINAL - BRASS, NICKEL PLATED
 INSULATOR - ABS
 NUT - BRASS, NICKEL PLATED
 WASHER - STEEL, NICKEL PLATED
 BODY TERMINAL - BRASS NICKEL PLATED


3. THIS PRODUCT IS RoHS COMPLIANT.

BULKHEAD PHONO JACK **BPJ** **F** **01** **AU** **X** RoHS COMPLIANT

FRONT MOUNT **PLATING**
 AU = GOLD
 BLANK = NICKEL

INSULATOR COLOR

01 = BLACK
 02 = RED
 03 = WHITE
 04 = YELLOW
 05 = BLUE
 06 = GREEN



CUSTOMER DRAWING

★ STAR SYMBOL DENOTES CRITICAL DIMENSION

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES
 - TWO PLACE DECIMALS ±0.01
 - THREE PLACE DECIMALS ±0.005
 - ANGLES ±1°
 - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.

2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002

3. REMOVE ALL BURRS

SIZE	WIDTH	MULT	LBS/M	TEMPER
------	-------	------	-------	--------

FINISH	MATERIAL
SPEC No.	SPEC No.

FIRST USED ON	SCALE
	2:1

DATE DRAWN	BY	CHKD	APVD
16-Mar-07	TJK	TJK	TJK

Switchcraft®

SHEET | OF |

NAME	PART No.	REV
RCA PHONO JACK FRONT MOUNT, RoHS	BPJF_X SERIES	A

DO NOT SCALE DRAWING

REV	ECO NUMBER	DATE	BY	APVD
A	26014	3-16-07	TJK	TJK

REVISIONS

Pro/Engineer CAD File

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[BPJF01](#) [BPJF01AUX](#) [BPJF02AUX](#) [BPJF02X](#) [BPJF03AUX](#) [BPJF03X](#) [BPJF04X](#) [BPJF05](#) [BPJR06AU](#) [BPJF06](#)
[BPJF06AU](#) [BPJF04AUX](#) [BPJF05X](#) [BPJF06AUX](#) [BPJF06X](#)