







NOTES:

1. PC TERMINAL ARRANGEMENT: 4,5.
2. CONTACT RATING 0.25 AMP, 30 WATTS MAX,
AC, NON - INDUCTIVE LOAD.
3. DIELECTRIC STRENGTH - 500 VOLTS, RMS. MIN.
4. SWITCH MOUNTS IN PANELS 0.047 TO 0.281 THICK.
POSITION 1: 0.047 - 0.094
POSITION 2: 0.094 - 0.141
POSITION 3: 0.141 - 0.188
POSITION 4: 0.188 - 0.234
POSITION 5: 0.234 - 0.281
5. MATERIALS:
HOUSING: THERMOPLASTIC, CHARCOAL GRAY
PUSHBUTTON: THERMOPLASTIC, COLOR (SEE CHART)
MOUNTING CLIP: COPPER ALLOY
CONTACT SPRINGS, INTEGRAL: COPPER ALLOY, SILVER PLATED
TERMINALS: COPPER ALLOY, SILVER PLATED
ACTUATOR: THERMOPLASTIC, BEIGE
SPRING: MUSIC WIRE, TINNED
RETAINER PLATE: PAPER EPOXY LAMINATE
6. THESE PRODUCTS ARE RoHS COMPLIANT.

PART NUMBER	PUSHBUTTON COLOR
BXR01IPC	RED
BXR02IPC	BLACK
BXR03IPC	GREEN
BXR05IPC	WHITE



CUSTOMER DRAWING



PANEL CUTOUT
SCALE 2:1

RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE
SCALE: 2=1

REV	ECO NUMBER	DATE	BY	APVD
B	27357	9-12-14	TO	TJK
A	22616	4-2-01	DA	RB
REV	ECO NUMBER	DATE	BY	APVD

★	STAR SYMBOL DENOTES CRITICAL DIMENSION
UNLESS OTHERWISE SPECIFIED	
1. ALL DIMENSIONS IN INCHES	
- TWO PLACE DECIMALS	±0.01
- THREE PLACE DECIMALS	±0.005
- ANGLES	±1°
- ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	
2. FEATURES ON THE SAME CENTERLINE	
MUST BE ALIGNED WITHIN ±0.002	
3. REMOVE ALL BURRS	
DO NOT SCALE DRAWING	

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON				SCALE 3:1		Switchcraft [®]			
DATE DRAWN	BY	CHKD		APVD					
30-Mar-01	DA	RB 4-6-01		RB 4-6-01					
NAME BXR SWITCH, MOMENTARY PC TERMINALS, RoHS					PART No. BXR01PC SERIES				REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[BXR011](#) [BXR0110](#) [BXR016PC](#) [BXR021](#) [BXR033](#) [BXR051](#) [BXR0510PC](#)