



**NOTES:**

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

**MATERIAL:**

- ⑥ HOUSING: POLYCARBONATE (REF: LEXAN 500)
- BUSHING & MTG. HARDWARE: NICKEL PLATED BRASS
- SLEEVE & SHUNT TERMINALS: SILVER PLATED COPPER ALLOY
- TIP TERMINAL: SILVER PLATED BERYLCO 25

CUSTOMER DRAWING

CAD/CAM DWG. NO.  
s.mdpc2ara\_cd  
SHEET 1 OF 1

REVISIONS				UNLESS OTHERWISE SPECIFIED				FINISH				MATERIAL										
ISSUE	CHANGE NO.	DATE	BY	APP'D	STAR SYMBOL DENOTES CRITICAL DIMENSION. SEE S/C ENGINEERING STANDARD ES-0001	SIZE	WIDTH	MULT	LBS./M	TEMPER	FINISH SPEC. NO.	MATERIAL SPEC. NO.	DATE DRAWN	BY	CHK'D	APP'D	SCALE	NAME	PART NO.	ISSUE		
G	ECO #21788	6-24-97	RC	JF	1. ALL DIMENSIONS IN INCHES TWO PLACE DECIMAL ±.01 THREE PLACE DECIMAL ±.005 FRACTIONAL DIMENSIONS ±1/64 ANGLES ±1/2° ALL DIA'S CONCENTRIC WITHIN .005 T.I.R. 2. REMOVE ALL BURRS 3. MAKE NO DIMENSIONAL ALLOWANCES FOR APPLIED FINISHES, I.E., PLATING, PAINTING, ETC. 4. HOLES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±.002								6-4-76	FGD	JRH	LG	1 = 0.100	MICRO-JACK	MDPC2ARA	G		
F	ECO #20627	1-25-96	DEA	TAO																		
E	ECO #20522	4-4-96	DEA	JF																		
D	ECO #20358	2-11-95	DEA	TAO																		
C	ECO #20212	2-11-95	DEA	TAO																		
B	REDRAWN ON CAD ECO #20206	2-11-95	DEA	TAO																		

Switchcraft®

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[MDPC2ARA](#)