







PCB LAYOUT
COMPONENT SIDE

CUSTOMER DRAWING

NOTES:


1. ALL DIMENSIONS ARE REFERENCE.
2. MATERIALS:
HOUSING: THERMOPLASTIC, BLACK
TERMINALS: COPPER ALLOY, SILVER PLATED
"AU" SUFFIX - GOLD PLATED
3. SUPPLIED ON TAPE & REEL, SEE SHEET 2.
4. THIS PRODUCT IS RoHS COMPLIANT

PART NUMBER (SEE NOTE 2)		
MDSMT2ARATRX	MDSMT2BRATRX	MDSMT3BRATRX
MDSMT2ARATRAUX	MDSMT2BRATRAUX	MDSMT3BRATRAUX

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
						SIZE	WIDTH		MULT	LBS/M	TEMPER		
						FINISH SPEC No.				MATERIAL SPEC No.			
						FIRST USED ON			SCALE 7.5		Switchcraft®		
						DATE DRAWN	BY	CHKD	APVD				
B	25810	1-31-08	TJK	TJK	06-Feb-06	JL	GG 2-6-06	GG 2-6-06		SHEET 1 OF 2			
A	25190	2-6-06	JL	GG									
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.	REV		
REVISIONS					DO NOT SCALE DRAWING					2.5 MM PHONE JACK SURFACE MOUNT, RoHS		MDSMT2-X-MDSMT3-X-SERIES	B


A: CARRIER SIZE

- 1. DETAIL SIZES REFERENCE: EIA-481
- 2. SPECIFICATION: 24 MM X 12 MM
- 3. COVER TAPE: SPECIFICATION ATTACHED (CONDUCTIVE)



B: REEL SIZE

- 1. QUANTITY: 1000 PCS/REEL
- 2. MATERIAL: THERMOPLASTIC



CUSTOMER DRAWING

SCALE NONE	Switchcraft®		
DATE DRAWN 06-Feb-06			
DRAWN BY JL	PART No. MDSMT2_X-MDSMT3_X-SERIES	SHEET 2 OF 2	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[MDSMT2ARATRX](#) [MDSMT2BRATRX](#) [MDSMT3BRATRX](#) [MDSMT4BRATRX](#)