

NOTES:

1. ALL DIMENSIONS ARE REFERENCE.

2. MATERIALS:

B HOUSING: ABS OR PBT, UL-94HB, BLACK




B COLOR INSERT: POM OR PBT, UL94-HB

SHELL & SLEEVE TERMINAL: COPPER ALLOY,NICKEL OR GOLD PLATED


TIP & SHUNT TERMINALS: COPPER ALLOY, TIN PLATED

3. THIS PART IS RoHS COMPLIANT

PART NUMBER	INSERT (A) COLOR	INSERT (B) COLOR	SHELL AND SLEEVE TERMINAL FINISH
PJ-RAN2X1U01X	RED	WHITE	NICKEL PLATED
PJ-RAN2X1U01AUX	RED	WHITE	GOLD PLATED
PJ-RAN2X1U02X	WHITE	RED	NICKEL PLATED
PJ-RAN2X1U02AUX	WHITE	RED	GOLD PLATED



P.C. BOARD LAYOUT
COMPONENT SIDE



SCHEMATIC
TYP (2) JACKS

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	SIZE		WIDTH		MULT		LBS/M		TEMPER			
						FINISH						MATERIAL					
						SPEC No.						SPEC No.					
						FIRST USED ON				SCALE 2:1		Switchcraft®					
						DATE DRAWN		BY	CHKD		APVD						
B	27929	08-17-17	PC	TJK		13-Jan-06		JL	TJK 1-13-06		TJK 1-13-06		SHEET 1 OF 1				
A	25181	1-13-06	JL	TJK		NAME						PART No.				REV	
REV	ECO NUMBER	DATE	BY	APVD		PHONO JACK, RIGHT ANGLE 2 POS, PC MOUNT, UNSHIELDED, RoHS						PJ-RAN2X1U__X SERIES				B	
REVISIONS					DO NOT SCALE DRAWING												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[PJРАН2Х1U01АUX](#) [PJРАН2Х1U02Х](#) [PJРАН2Х1U01](#) [PJРАН2Х1U02AU](#) [PJРАН2Х1U02](#) [PJРАН2Х1U01Х](#)
[PJРАН2Х1U02АUX](#)