

NOTES:

1. ALL DIMENSIONS ARE REFERENCE.
2. MATERIALS:




B

HOUSING: ABS, UL-94HB, BLACK

B

SHELL & SLEEVE TERMINALS: COPPER ALLOY,
SEE TABLE FOR FINISH


TIP & SHUNT TERMINALS: COPPER ALLOY, TIN PLATED
3. THIS PART IS RoHS COMPLIANT



P.C. BOARD LAYOUT
COMPONENT SIDE

PART NUMBER	INSERT (A)	INSERT (B)	INSERT (C)	SHELL AND SLEEVE TERMINAL FINISH
PJ-RAN3XIU01X	RED	WHITE	YELLOW	NICKEL PLATED
PJ-RAN3XIU01AUX	RED	WHITE	YELLOW	GOLD PLATED
PJ-RAN3XIU02X	SEE SEPARATE DRAWING			
PJ-RAN3XIU02AUX	SEE SEPARATE DRAWING			
PJ-RAN3XIU03X	RED	GREEN	BLUE	NICKEL PLATED
PJ-RAN3XIU03AUX	RED	GREEN	BLUE	GOLD PLATED
PJ-RAN3XIU04X	YELLOW	RED	WHITE	NICKEL PLATED
PJ-RAN3XIU05X	RED	YELLOW	WHITE	NICKEL PLATED

CUSTOMER DRAWING



					★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.								
						SIZE	WIDTH		MULT	LBS/M	TEMPER			
						FINISH SPEC No.				MATERIAL SPEC No.				
						FIRST USED ON			SCALE 2:1		Switchcraft® SHEET OF			
						DATE DRAWN	BY	CHKD	APVD					
B	26316	1-7-09	TJK	TJK		13-Jan-06	JL	TJK 1-13-06	TJK 1-13-06					
A	25181	1-13-06	JL	TJK										
REV	ECO NUMBER	DATE	BY	APVD		NAME PHONO JACK, RIGHT ANGLE 3 POS, PC MOUNT, UNSHIELDED RoHS				PART No. PJ-RAN3XIU__X SERIES			REV B	
REVISIONS					DO NOT SCALE DRAWING									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[PJРАН3Х1U01Х](#) [PJРАН3Х1U03Х](#) [PJРАН3Х1U01AU](#) [PJРАН3Х1U02AU](#) [PJРАН3Х1U03](#)