






NOTES:

1. ALL DIMENSIONS ARE REFERENCE.
2. MATERIALS:
- B** HOUSING: ABS OR PBT, UL-94HB, BLACK
- B** COLOR INSERT: POM OR PBT, UL-94HB
- SHELL & SLEEVE TERMINALS: COPPER ALLOY, NICKEL OR GOLD PLATED
- TIP TERMINALS: COPPER ALLOY, TIN PLATED
- FRONT PLATE: COPPER ALLOY, NICKEL PLATED
3. THIS PART IS RoHS COMPLIANT

PART NUMBER	INSERT (A) COLOR	INSERT (B) COLOR	SHELL AND SLEEVE TERMINAL FINISH
PJRAS2X1S01X	RED	WHITE	NICKEL PLATED
PJRAS2X1S01AUX	RED	WHITE	GOLD PLATED
PJRAS2X1S02X	WHITE	RED	NICKEL PLATED
PJRAS2X1S02AUX	WHITE	RED	GOLD PLATED



P.C. BOARD LAYOUT
COMPONENT SIDE



SCHEMATIC
TYP (2) JACKS

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	SIZE		WIDTH		MULT		LBS/M		TEMPER			
						FINISH					MATERIAL						
						SPEC No.					SPEC No.						
						FIRST USED ON			SCALE			Switchcraft®					
									2:1								
B	27929	08-17-17	PC	TJK		DATE DRAWN	BY	CHKD		APVD		SHEET 1 OF 1					
A	25181	1-13-06	JL	TJK		13-Jan-06	JL	TJK 1-13-06		TJK 1-13-06							
REV	ECO NUMBER	DATE	BY	APVD		NAME		PHONO JACK, RIGHT ANGLE, 2 POS. SCREW MOUNT, SHIELDED, RoHS						PART No.		REV	
REVISIONS					DO NOT SCALE DRAWING							PJRAS2X1S__X SERIES				B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[PJRAS2X1S01AUX](#) [PJRAS2X1S01X](#) [PJRAS2X1S02](#) [PJRAS2X1S02AUX](#)