



NOTES:

1. DIMENSIONS IN MILLIMETERS [INCHES].
2. TAPE CONFORMS TO ANSI/EIA-481.
3. MAXIMUM COMPONENT ROTATION WITHIN CAVITY 20°.
4. REEL SIZE 22 INCH., PLASTIC
5. PART QUANTITY PER REEL: 375.
6. ALL DIMENSIONS ARE REFERENCE
7. THIS PRODUCT IS RoHS COMPLIANT

PART NUMBER	PART REV.	POWER JACK
RASM712PTRP22X	A	RASM712PX
RASM722PTRP22X	A	RASM722PX
RASM732PTRP22X	A	RASM732PX

CUSTOMER DRAWING

					<div>★ STAR SYMBOL DENOTES CRITICAL DIMENSION</div> <div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.</div> <div>2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002</div> <div>3. REMOVE ALL BURRS</div> <div>DO NOT SCALE DRAWING</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
						SIZE	WIDTH		MULT	LBS/M	TEMPER
						FINISH				MATERIAL	
						SPEC No.				SPEC No.	
						FIRST USED ON			SCALE 1:4		
						DATE DRAWN	BY	CHKD	APVD		
A	25129	9-6-05	JL	MW	06-Sep-05	JL	MW 9-6-05	MW 9-6-05			
REV ECO NUMBER DATE BY APVD					NAME RASM POWER JACK WITH POST TAPE & REEL 22". RoHS					PART No. RASM7_2PTRP22X	REV A
REVISIONS											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[RASM712PTRP22X](#) [RASM732PTRP22X](#)