



PART NUMBER	PART REV.	POWER JACK
RASM712TRP22X	A	RASM712X
RASM722TRP22X	A	RASM722X
RASM732TRP22X	A	RASM732X

NOTES:

- DIMENSIONS IN MILLIMETERS [INCHES].
- TAPE CONFORMS TO ANSI/EIA-481.
- MAXIMUM COMPONENT ROTATION WITHIN CAVITY 20°.
- REEL SIZE 22 INCH., PLASTIC
- PART QUANTITY PER REEL: 560.
- ALL DIMENSIONS ARE REFERENCE
- THIS PRODUCT IS RoHS COMPLIANT

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	SIZE		WIDTH		MULT		LBS/M		TEMPER			
						FINISH						MATERIAL					
						SPEC No.						SPEC No.					
						FIRST USED ON				SCALE		Switchcraft®					
										1:4							
						DATE DRAWN		BY	CHKD		APVD						
A	25888	6-19-08	JEB	TJK	17-Oct-08		JEB	JEB 10-17-08		TJK 10-17-08							
REV	ECO NUMBER	DATE	BY	APVD					NAME		PART No.		REV				
REVISIONS									RASM POWER JACK TAPE & REEL 22", PLASTIC, RoHS		RASM7_2TRP22X		A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[RASM722TRP15X](#) [RASM732TRP22X](#)