




SWITCHCRAFT CATALOG PART NUMBER



CURRENT CARRYING CAPACITY	
1A, 100V AC	
2A, 12V DC	
INSULATION RESISTANCE:	50MΩ MIN
DIELECTRIC STRENGTH:	250V DC/1 MINUTE
CONTACT RESISTANCE:	30mΩ MAX I
INSERTION FORCE:	0.8~5 KG / 1.76~11lb
EXTRACTION FORCE:	0.8~4 KG / 1.76~8.8lb

REVISIONS				STAR SYMBOL DENOTES CRITICAL DIMENSION. SEE S/C ENGINEERING STANDARD ES-0001.				THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSE ONLY.			
DATE	BY	CHK'D	APP'D	FINISH	SILVER PLATE	MATERIAL	SPEC. NO.	SIZE	WIDTH	WULT	TEMPER
9-6-90	SG	EB	DV	DATE DRAWN	SCALE	NTS					
NAME	MINI DIN				PART NO. SMD3/SMD8FRA110				ISSUE E		

CUSTOMER DRAWING

CAD/CAM DWG. NO. SMD3-SMD8FRA110_CD

SHEET 1 OF 1

Pro/Engineer CAD File

ROUTING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[SMD4FRA110](#) [SMD3FRA110](#) [SMD5FRA110](#) [SMD6FRA110](#) [SMD7FRA110](#)