




APPROVED: _____

DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A	11345	REDRAWN	5/09/11	
B	11345	Revised specs, material and operating temp	9/7/12	
C	11345	REDRAWN	3/12/13	
D	11345	REDRAWN	6/14/13	
E	11345	ADDED SPEC.	3/20/14	HR/KW
F	11345	REVISED SPEC.	9/17/15	AY/MW



SPECIFICATIONS:

Material:

Insulator: Polyamide, rated UL 94V-0,

Insulator color: Natural

Contacts: Copper Alloy

Plating:

Tin plated over Copper underplate overall

Electrical:

Voltage rating: 30V DC

Current rating: 0.5A AC/DC (32 Awg wire)

0.2A AC/DC (36 Awg wire)

Contact resistance: 20 mohms max

Insulation resistance: 100MΩ min

Dielectric withstanding voltage: 200V AC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 20, 22

A = .031 [0.80] x No. of Spaces

B = .031 [0.80] x No. of Spaces + .063 [1.60]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	BW	01/17/07
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE			
0.8mm HOUSING IDC TYPE			
SIZE X	PART NO. 08CH-A-XX-IDC	REV. F	
REF: S00015T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[08CH-A-03-IDC](#) [08CH-A-04-IDC](#) [08CH-A-09-IDC](#) [08CH-A-08-IDC](#) [08CH-A-02-IDC](#) [08CH-A-10-IDC](#) [08CH-A-05-IDC](#) [08CH-A-06-IDC](#)