




Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A		REDRAWN	8/20/09	
B		REVISED SHAPE	3/21/13	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Polyimide, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Solder Tab: Brass
Plating: Tin plated over Copper underplate overall
Electrical:
Voltage rating: 250V AC/DC
Current rating: 0.5A AC/DC (32 Awg wire)
0.2A AC/DC (36 Awg wire)
Contact resistance: 20 mohms max
Insulation resistance: 100MΩ min
Dielectric withstanding voltage: 200V AC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant

PACKAGED ON TAPE & REEL

Positions: 02 thru 17, 20, 22
A = .031 [0.80] x No. of Spaces
B = .031 [0.80] x No. of Spaces + .118 [3.00]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
X .10 ± .10 ØX ± .10 .XX .020 ± .015 ØXX ± .015 .XXX .015 ± .010 ØXXX ± .010		TITLE .031 [0.80] PITCH HEADER, STRAIGHT TYPE	
APPROVALS	DATE		
DRAWN	BW	01/17/07	
CHECKED			
APPROVED			
SIZE PART NO. 08SH-A-XX-TS-SMT		REV. B	
REF: S00015T		SCALE: NTS SHEET 1 OF 1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[08SH-A-07-TS-SMT](#)