





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		REVISED SPEC.	6/7/12	



NOTE: 1 LOCK ON 2 & 3 POSITION

Positions: 2 thru 15
A = .049 [1.25] x No. of Positions-1
B = .049 [1.25] x No. of Positions + .068 [1.75]

SPECIFICATIONS:
Material:
Insulator: PBT, rated UL 94V-0
Insulator color: White
Electrical:
Operating voltage: 125 VAC max
Current rating: 1 Amp max
Insulation resistance: 100 Mohms min @ 500 VDC
Dielectric withstanding voltage: 250 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.049" [1.25mm] CRIMP HOUSING
LOW PROFILE, DUAL POLARIZED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH			
HOLES				909 Rahway Avenue, Union, NJ 07083			
.X	± .10	Ø.X	± .10	Phone: 908-687-5000 Fax: 908-687-5710			
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS			DATE				
DRAWN	SS	4/6/05					
CHECKED							
APPROVED							
SIZE		PART NO.		REV.			
X		125CH-A-XX		A			
REF:		SCALE: NTS		SHEET 1 OF 1			
.049" [1.25mm] CRIMP HOUSING LOW PROFILE, DUAL POLARIZED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125CH-A-04](#) [125CH-A-05](#) [125CH-A-06](#) [125CH-A-10](#) [125CH-A-02](#) [125CH-A-09](#) [125CH-A-14](#) [125CH-A-15](#) [125CH-A-07](#) [125CH-A-08](#) [125CH-A-11](#) [125CH-A-13](#) [125CH-A-12](#) [125CH-A-03](#)