







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A		REVISED COLOR	6/21/10	
B		UPDATE DRAWING	10/25/17	AY/NC



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Electrical:

Voltage rating: 125 VAC/DC

Current rating: 1 A AC/DC

Contact resistance: 20 mohms max.

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

-40°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 15

A = .049 [1.25] x No. of Spaces

B = .049 [1.25] x No. of Spaces + .118 [3.00]

C = .049 [1.25] x No. of Spaces + .067 [1.70]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN

BW

01/17/07

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

1.25mm HOUSING

SIZE

X

PART NO.

125CH-B-XX

REV.

C

REF: S00124T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125CH-B-09](#) [125CH-B-04](#) [125CH-B-02](#) [125CH-B-15](#) [125CH-B-03](#) [125CH-B-14](#) [125CH-B-06](#) [125CH-B-08](#) [125CH-B-10](#) [125CH-B-13](#) [125CH-B-05](#) [125CH-B-07](#) [125CH-B-11](#) [125CH-B-12](#)