

6

5

4

3

2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/17/16	

D

D

C




C

B

B

A

A

**SPECIFICATIONS:**

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: Beige

**Electrical:**

Voltage rating: 250 VAC/DC

Current rating: 1A AC/DC

Contact resistance: 10 mohms max

Insulation resistance: 1,000Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

**Temperature Rating:**

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 10, 11, 12, 14, 15, 20, 25, 30

A =.049 [1.25] X No. of Spaces

B =.049 [1.25] X No. of Spaces + .071 [1.80]

C =.049 [1.25] X No. of Spaces + .114 [2.90]

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	3/17/16
CHECKED	SC	3/17/16
APPROVED		

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
1.25mm CRIMP HOUSING SINGLE ROW  
2 THRU 30 POSITIONS, COLOR: GRAY

SIZE X	PART NO. 125CH-C1-XX	REV. -
REF: S00015T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125CH-C1-06](#) [125CH-C1-13](#) [125CH-C1-07](#) [125CH-C1-10](#) [125CH-C1-11](#) [125CH-C1-03](#) [125CH-C1-05](#) [125CH-C1-04](#) [125CH-C1-14](#) [125CH-C1-12](#) [125CH-C1-15](#) [125CH-C1-02](#) [125CH-C1-09](#) [125CH-C1-08](#)