


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/11/08	
A		REVISED SHAPE	11/18/10	
B		REVISED COLOR	5/27/11	



SPECIFICATIONS:

Material:
 Insulator: Nylon 66, rated UL 94V-0
 Insulator color: Beige

Electrical:
 Voltage rating: 100V AC/DC
 Current rating: 1A AC/DC max
 Insulation resistance: 500 Mohms min
 Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



Positions: 2 thru 10, 12, 15, 20, 25, 30
 A = .049 [1.25] X No. of positions - 1
 B = .049 [1.25] X No. of positions + .077 [1.95]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN SS 11/11/08 CHECKED APPROVED			TITLE 1.25mm CRIMP HOUSING SINGLE ROW 2 THRU 30 POSITIONS, COLOR: BEIGE		
DATE 11/11/08			SIZE X	PART NO. 125CH-D-XX	REV. B
REF: S00123T			SCALE: NTS		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125CH-D-07](#) [125CH-D-12](#) [125CH-D-10](#) [125CH-D-02](#) [125CH-D-09](#) [125CH-D-13](#) [125CH-D-04](#) [125CH-D-06](#)
[125CH-D-03](#) [125CH-D-14](#) [125CH-D-05](#) [125CH-D-15](#) [125CH-D-08](#) [125CH-D-11](#)