



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/30/10	
A		REVISED SHAPE	6/18/12	



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: White

Electrical:

Voltage rating: 125 VAC/DC max

Current rating: 1 Amp max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 16, 18, 20, 22, 24, 26, 28, 30
A = .049 [1.25] X No. of Spaces
B = .049 [1.25] X No. of Spaces + .057 [1.45]
C = .049 [1.25] X No. of Spaces - .049 [1.25]
DIM. C 2P, 3P (NONE)

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.049 [1.25] PITCH CRIMP HOUSING

SINGLE ROW, 2 THRU 30 POSITIONS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				TITLE			
.X	± .10	ØX	± .10	HOLE			
.XX	± .020	ØXX	± .015	HOLE			
.XXX	± .015	ØXXX	± .010	HOLE			
APPROVALS				DATE			
DRAWN	AY		11/30/10				
CHECKED	AH		11/30/10				
APPROVED							
REF: S00123T				SCALE: NTS			
SHEET 1 OF 1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125CH-G-09](#) [125CH-G-13](#) [125CH-G-03](#) [125CH-G-12](#) [125CH-G-05](#) [125CH-G-11](#) [125CH-G-08](#) [125CH-G-02](#)
[125CH-G-16](#) [125CH-G-07](#) [125CH-G-15](#) [125CH-G-06](#) [125CH-G-04](#) [125CH-G-14](#) [125CH-G-10](#)