




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REDRAWN	1/29/10	



RECOMMENDED PCB LAYOUT

CIRCUITS	DIM A	DIM B
2	.049 [1.25]	.169 [4.30]
3	.098 [2.50]	.217 [5.50]
4	.148 [3.75]	.268 [6.80]
5	.197 [5.00]	.315 [8.00]
6	.246 [6.25]	.366 [9.30]
7	.295 [7.50]	.413 [10.50]
8	.344 [8.75]	.465 [11.80]
9	.394 [10.00]	.512 [13.00]
10	.443 [11.25]	.563 [14.30]
11	.492 [12.50]	.610 [15.50]
12	.541 [13.75]	.661 [16.80]
13	.591 [15.00]	.709 [18.00]
14	.640 [16.25]	.760 [19.30]
15	.689 [17.50]	.807 [20.50]



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 125 VAC, DC

Current rating: 1A AC, DC

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.049 [1.25] SINGLE ROW HEADER,
VERTICAL, STRAIGHT, DIP TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH			
HOLES				909 Rahway Avenue, Union, NJ 07083			
.X	± .10	ØX	± .10	Phone: 908-687-5000 Fax: 908-687-5710			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS			TITLE				
			.049 [1.25] SINGLE ROW HEADER, VERTICAL, STRAIGHT, DIP TYPE				
DRAWN	BW	01/17/07		SIZE	PART NO.	REV.	
CHECKED				X	125SH-A-XX-TS	A	
APPROVED				REF: S00016T	SCALE: NTS	SHEET 1	OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-A-02-TS](#) [125SH-A-03-TS](#) [125SH-A-04-TS](#) [125SH-A-05-TS](#) [125SH-A-06-TS](#) [125SH-A-07-TS](#) [125SH-A-14-TS](#) [125SH-A-10-TS](#) [125SH-A-12-TS](#) [125SH-A-09-TS](#) [125SH-A-11-TS](#) [125SH-A-08-TS](#) [125SH-A-13-TS](#) [125SH-A-15-TS](#)