





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	7553	RELEASED	02/23/07	



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



A=.049 [1.25] X No. of Spaces

B=.049 [1.25] X No. of Spaces + .070 [1.80]

C=.049 [1.25] X No. of Spaces +.118 [3.00]

D=.049 [1.25] X No. of Spaces + .251 [6.40]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	BW	02/23/07
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
MX 1.25mm WAFER SMT STRAIGHT

SIZE X	PART NO. 125SH-A-XX-TS-SMT	REV. -
REF:	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-A-04-TS-SMT](#) [125SH-A-05-TS-SMT](#) [125SH-A-07-TS-SMT](#) [125SH-A-14-TS-SMT](#) [125SH-A-03-TS-SMT](#)
[125SH-A-11-TS-SMT](#) [125SH-A-13-TS-SMT](#) [125SH-A-02-TS-SMT](#) [125SH-A-15-TS-SMT](#) [125SH-A-08-TS-SMT](#)
[125SH-A-12-TS-SMT](#) [125SH-A-09-TS-SMT](#) [125SH-A-06-TS-SMT](#) [125SH-A-10-TS-SMT](#)