




DATE: _____ TITLE: _____


$$A = .049 [1.25] \times \text{No. of Spaces}$$
$$B = .049 [1.25] \times \text{No. of Spaces} + .118 [3.00]$$
$$C = .049 \begin{bmatrix} 1.25 \end{bmatrix} \times \text{No. of Spaces} + .071 \begin{bmatrix} 1.80 \end{bmatrix}$$
$$D = .049 [1.25] \times \text{No. of Spaces} + .230 [5.85]$$

PACKAGED ON TAPE & REEL

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Solder nail: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Current rating: 1 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Temperature Rating
-40°C to +85°C

Environmental:

Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

INCHES		MILLIMETERS	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
WN	RW	01/17/07

OWN	BW	01/11/07
CKED		

PROVED		
--------	--	--

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
MX 1.25mm WAFER 90° SMT			
SIZE X	PART NO. 125SH-B-XX-TR-SMT-T/R		REV C
REF: S00124T	SCALE: NTS	SHEET 1 OF 1	

RoHS
COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-B-10-TR-SMT-T/R](#) [125SH-B-08-TR-SMT-T/R](#) [125SH-B-03-TR-SMT-T/R](#) [125SH-B-04-TR-SMT-T/R](#) [125SH-B-09-TR-SMT-T/R](#) [125SH-B-02-TR-SMT-T/R](#) [125SH-B-07-TR-SMT-T/R](#) [125SH-B-05-TR-SMT-T/R](#) [125SH-B-06-TR-SMT-T/R](#)