





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	11227	RELEASED	4/11/11	
A		REVISED SHAPE & SPEC.	4/10/12	
B		UPDATE DRAWING	11/8/17	AY/TY



PACKAGED ON TAPE & REEL

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Solder Tabs: Brass, Tin plated

Electrical:

Voltage rating: 100V AC,DC

Current rating: 1A AC,DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Withstanding voltage: 500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15

A = .049 [1.25] X No. of Spaces

B = .049 [1.25] X No. of Spaces + .114 [2.90]

C = .049 [1.25] X No. of Spaces + .197 [5.00]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE .049 [1.25] PITCH WIRE TO BOARD HEADER STRAIGHT, SMT TYPE		
DATE			SIZE		
DRAWN DY 4/11/11			PART NO. 125SH-C-XX-TS-SMT-T/R		
CHECKED			REV. B		
APPROVED			REF: S00123T		
			SCALE: NTS		
			SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-C-07-TS-SMT-T/R](#) [125SH-C-06-TS-SMT-TR](#) [125SH-C-08-TS-SMT-TR](#) [125SH-C-05-TS-SMT-T/R](#) [125SH-C-03-TS-SMT-TR](#) [125SH-C-10-TS-SMT-TR](#) [125SH-C-03-TS-SMT-T/R](#) [125SH-C-08-TS-SMT-T/R](#) [125SH-C-09-TS-SMT-TR](#) [125SH-C-04-TS-SMT-TR](#) [125SH-C-09-TS-SMT-T/R](#) [125SH-C-04-TS-SMT-T/R](#) [125SH-C-10-TS-SMT-T/R](#) [125SH-C-07-TS-SMT-TR](#) [125SH-C-02-TS-SMT-TR](#) [125SH-C-02-TS-SMT-T/R](#) [125SH-C-05-TS-SMT-TR](#) [125SH-C-06-TS-SMT-T/R](#)