





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED SPECIFICATIONS	7/28/09	
B		REVISED SHAPE	3/23/11	
C		UPDATE DRAWING	1/19/19	AY/TY



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Electrical:

Current rating: 1A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15

A = .059 [1.50] X No. of Spaces.

B = .059 [1.50] X No. of Spaces + .118 [3.00].

C = .059 [1.50] X No. of Spaces + .075 [1.90].

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN	BW	01/17/07
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

ZH 1.50mm HOUSING

SIZE

X

PART NO.

15CH-A-XX

REV.

B

REF: S00124T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15CH-A-12](#) [15CH-A-04](#) [15CH-A-02](#) [15CH-A-07](#) [15CH-A-08](#) [15CH-A-15](#) [15CH-A-09](#) [15CH-A-11](#) [15CH-A-06](#)
[15CH-A-14](#) [15CH-A-13](#) [15CH-A-03](#) [15CH-A-05](#) [15CH-A-10](#)