




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	



CIRCUIT 1

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Ivory

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 1.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



A=.059 [1.50] X NO. OF SPACES

B=.059 [1.50] X NO. OF SPACES +.102 [2.60]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN CHECKED APPROVED			DATE 01/17/07 PART NO. 15CH-B-XX REV. -		
REF:			SCALE: NTS SHEET 1 OF 1		

TITLE
 MX1.5mm HOUSING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15CH-B-11](#) [15CH-B-15](#) [15CH-B-12](#) [15CH-B-13](#) [15CH-B-09](#) [15CH-B-06](#) [15CH-B-02](#) [15CH-B-03](#) [15CH-B-04](#)
[15CH-B-14](#) [15CH-B-05](#) [15CH-B-07](#) [15CH-B-10](#) [15CH-B-08](#)