




APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A		UPDATED SPECIFICATIONS	7/28/09	
B		UPDATE DRAWING	9/12/17	AY/NC



SECTION A-A



SECTION B-B



SECTION C-C

SPECIFICATIONS:

Material:

Contact: Phospher Bronze

Plating:

Tin over Nickel underplate overall

Electrical:

Current rating: 1A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 mohms min.

Withstan Voltage: 500V AC/Minuite

Mechanical:

Applicable Wires: 28~32 AWG

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN

BW

01/17/07

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

ZH 1.5mm TERMINAL

SIZE
X

PART NO.

15CTA-R

REV.
B

REF: S00124T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15CTA-R](#)