

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|----------|------|
| - | | RELEASED | 12/22/08 | |

RECOMMENDED
PCB LAYOUT**SPECIFICATIONS:****Material:**

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Ivory

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 1.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

**DIMENSIONS**

A = .059 [1.50] X No OF POSITIONS - 1

B = .059 [1.50] X No OF POSITIONS + .059 [1.50]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

| INCHES | HOLES |
|-------------|--------------|
| .X ± .10 | Ø.X ± .10 |
| .XX ± .020 | Ø.XX ± .015 |
| .XXX ± .015 | Ø.XXX ± .010 |

| APPROVALS | | DATE |
|-----------|----|----------|
| DRAWN | SS | 12/22/08 |
| CHECKED | | |
| APPROVED | | |

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.059 [1.5mm] HEADER, RIGHT ANGLE

| | | |
|-----------|--------------------------|--------------|
| SIZE X | PART NO. 15SH-A-XX-TR | REV. - |
| REF: | SCALE: NTS | SHEET 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15SH-A-04-TR](#) [15SH-A-05-TR](#) [15SH-A-06-TR](#) [15SH-A-03-TR](#) [15SH-A-13-TR](#) [15SH-A-11-TR](#) [15SH-A-12-TR](#)
[15SH-A-10-TR](#) [15SH-A-09-TR](#) [15SH-A-02-TR](#) [15SH-A-08-TR](#) [15SH-A-15-TR](#) [15SH-A-07-TR](#) [15SH-A-14-TR](#)