





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/31/08	
A		REVISED SHAPE	11/04/09	
B		REVISED DIM.	3/6/13	
C		UPDATE DRAWING	10/31/19	LH/KL



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
 Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
 Insulator color: Ivory
 Contacts: Brass
 Solder Tab: Phosphor Bronze
 Plating:
 Tin over Nickel underplate overall
 Electrical:
 Voltage rating: 50 VAC/DC
 Current rating: 1 Amp (26AWG)
 Contact resistance: 20 mohms max
 Insulation resistance: 500 Mohms min
 Dielectric withstanding voltage: 500 VAC for 1 minute
 Mechanical:
 Applicable Wire: #32~#26AWG
 Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



Positions: 02 thru 16

A = .059 [1.50] x No. of Spaces

B = .059 [1.50] x No. of Positions + .118 [3.00]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE					
DRAWN		SS		1/31/08		MX1.5mm WAFER 90°, SMT	
CHECKED							
APPROVED							
REF:		S00123T		SCALE: NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15SH-A-07-TR-SMT](#) [15SH-A-15-TR-SMT](#) [15SH-A-09-TR-SMT](#) [15SH-A-03-TR-SMT](#) [15SH-A-02-TR-SMT](#) [15SH-A-10-TR-SMT](#) [15SH-A-14-TR-SMT](#) [15SH-A-05-TR-SMT](#) [15SH-A-06-TR-SMT](#) [15SH-A-13-TR-SMT](#) [15SH-A-12-TR-SMT](#)
[15SH-A-08-TR-SMT](#) [15SH-A-11-TR-SMT](#) [15SH-A-04-TR-SMT](#)