





APPROVED: _____
DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	8/14/09	
A		ADDED DIM.	4/6/11	
B		ADDED CONTACTS TOLERANCES	11/5/15	AY/RT
C		UPDATE DRAWING	5/16/18	AY/MY



RECOMMENDED PCB LAYOUT



RECOMMENDED ASSEMBLY DIM.



SECTION A-A

Kink						
Circuit	Circuit No.					
	1	2	3	4	5	6~13
2	Kink	Kink				
3	Kink		Kink			
4	Kink			Kink		
5~13	N	Kink			Kink	N

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Beige

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 50 V AC/DC

Current rating: 1 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 13

A=.059 [1.50] X No. of Spaces

B=.059 [1.50] X No. of Positions + .059 [1.50]

c=.059 [1.50] X No. of Positions + .024 [0.60]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	DY	8/14/09
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
.059 [1.50] VERTICAL HEADER			
SIZE	PART NO.	REV.	
X	15SH-A-XX-TS	C	
REF:	S00124T	SCALE:	NTS
SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15SH-A-04-TS](#) [15SH-A-05-TS](#) [15SH-A-06-TS](#) [15SH-A-11-TS](#) [15SH-A-14-TS](#) [15SH-A-08-TS](#) [15SH-A-03-TS](#)
[15SH-A-13-TS](#) [15SH-A-12-TS](#) [15SH-A-02-TS](#) [15SH-A-09-TS](#) [15SH-A-07-TS](#) [15SH-A-15-TS](#) [15SH-A-10-TS](#)