

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-	7790	RELEASED	5/10/07	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Ivory

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 1.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



A=.060 [1.50] X No. of Positions -1
B=.060 [1.50] X No. of Positions + .051 [1.30]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MX1.5mm WAFER 180°

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	BW		5/10/07				
CHECKED							
APPROVED							
				TITLE			
				MX1.5mm WAFER 180°			
				SIZE PART NO.			
				X 15SH-B-XX-TS-SMT			
				SCALE: NTS			
				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[15SH-B-02-TS-SMT](#) [15SH-B-07-TS-SMT](#) [15SH-B-13-TS-SMT](#) [15SH-B-05-TS-SMT](#) [15SH-B-09-TS-SMT](#) [15SH-B-08-TS-SMT](#) [15SH-B-12-TS-SMT](#) [15SH-B-10-TS-SMT](#) [15SH-B-03-TS-SMT](#) [15SH-B-06-TS-SMT](#) [15SH-B-15-TS-SMT](#)
[15SH-B-11-TS-SMT](#) [15SH-B-04-TS-SMT](#) [15SH-B-14-TS-SMT](#)