




Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED COLOR	9/24/10	
B		REVISED SPEC.	9/26/13	AV/SL

APPROVED: _____

DATE: _____ TITLE: _____



POLES	DIMENSIONS INCHES [mm]	
	A	B
2	.039 [1.00]	.197 [5.00]
3	.079 [2.00]	.236 [6.00]
4	.118 [3.00]	.276 [7.00]
5	.157 [4.00]	.315 [8.00]
6	.197 [5.00]	.354 [9.00]
7	.236 [6.00]	.394 [10.00]
8	.276 [7.00]	.433 [11.00]
9	.315 [8.00]	.472 [12.00]
10	.354 [9.00]	.512 [13.00]
11	.394 [10.00]	.551 [14.00]
12	.433 [11.00]	.591 [15.00]
13	.472 [12.00]	.630 [16.00]
14	.512 [13.00]	.669 [17.00]
15	.551 [14.00]	.709 [18.00]
16	.591 [15.00]	.748 [19.00]
17	.630 [16.00]	.787 [20.00]
18	.669 [17.00]	.827 [21.00]
19	.709 [18.00]	.866 [22.00]
20	.748 [19.00]	.906 [23.00]

SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-0

Insulator color: White

Electrical:

Operating voltage: 50 VAC max

Current rating: 1 Amp AC, DC max

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Contact resistance: 20 mohms max.

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

1.0mm CRIMP HOUSING

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .015	ØXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .010	ØXXX	± .010
APPROVALS				DATE			
DRAWN	BW		01/17/07				
CHECKED							
APPROVED							
				TITLE			
				1.0mm CRIMP HOUSING			
				SIZE			
				X			
				PART NO.			
				1CH-A-XX			
				REV.			
				B			
				SCALE: NTS			
				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[1CH-A-12](#) [1CH-A-15](#) [1CH-A-05](#) [1CH-A-11](#) [1CH-A-03](#) [1CH-A-02](#) [1CH-A-04](#) [1CH-A-10](#) [1CH-A-07](#) [1CH-A-09](#)
[1CH-A-14](#) [1CH-A-06](#) [1CH-A-08](#) [1CH-A-13](#)