

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		REDRAWN	1/10/14	AY/LL



SPECIFICATIONS:

Material:

Insulator: Nylon 66 UL 94V-0

Insulator color: White

Electrical:

Operating voltage: 250 V AC/DC

Current rating: 3A AC/DC

Insulation resistance: 1,000Mohms Min.

Dielectric withstanding voltage: 800V AC for 1 MIN.

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Spaces + .169 [4.30]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE WIRE TO BOARD PITCH: 2.5MM CRIMP HOUSING		
DRAWN	LFJ	4/13/06	SIZE X	PART NO. 25CH-C-XX	REV. A
CHECKED			REF: S00016T	SCALE: NTS	SHEET 1 OF 1
APPROVED					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25CH-C-04](#) [25CH-C-02](#) [25CH-C-06](#) [25CH-C-08](#) [25CH-C-11](#) [25CH-C-10](#) [25CH-C-15](#) [25CH-C-03](#) [25CH-C-14](#)
[25CH-C-07](#) [25CH-C-05](#) [25CH-C-13](#) [25CH-C-12](#) [25CH-C-09](#)