




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/10/10	
A		REVISED DIM.	10/25/10	



SPECIFICATIONS:

Material:
 Insulator: Nylon 66 UL 94V-0
 Insulator color: Natural

Electrical:
 Operating voltage: 250 VAC
 Current rating: 3 Amp max
 Contact Resistance: 20 mohms max
 Insulation resistance: 1,000Mohms MIN.
 Dielectric withstanding voltage: 1,000V AC for 1 MIN.

Temperature Rating:
 Temperature range: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



Positions: 02 thru 20
 A = .098 [2.50] x No. of Spaces
 B = .098 [2.50] x No. of Spaces + .154 [3.90]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN DY 2/10/10 CHECKED APPROVED			TITLE SHROUDED CRIMP TERMINAL HOUSING		
SIZE X PART NO. 25CH-E-XX REF: S00123T			REV. A SCALE: NTS SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25CH-E-07](#) [25CH-E-02](#) [25CH-E-11](#) [25CH-E-10](#) [25CH-E-04](#) [25CH-E-12](#) [25CH-E-13](#) [25CH-E-05](#) [25CH-E-03](#)
[25CH-E-14](#) [25CH-E-15](#) [25CH-E-09](#) [25CH-E-06](#) [25CH-E-08](#)