





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/08/09	
A		UPDATE DIM. & SPEC.	2/10/20	AY/RC
B		UPDATE DIM. & SPEC.	2/22/21	LH/EY
C		UPDATE DIM. & SPEC.	2/24/21	LH/EY



SECTION A-A



SECTION B-B

SPECIFICATIONS:

Material:

Contact: Phosphor Bronze, Thickness= 0.20mm

Plating:

Tin over Copper underplate overall

Electrical:

Wire range: 24-28 AWG

Insulation O.D: 1.70mm (max)

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	6/08/09
CHECKED		
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
2.50MM PITCH CRIMP TERMINAL			
SIZE X	PART NO. 25CTC-R	REV. C	
REF: S00016T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25CTC-R](#)