





APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	2/10/10	
A		REVISED SPEC.	5/15/13	
B		UPDATED DRAWING	3/15/17	HR/CH



SECTION A-A



SECTION B-B



SPECIFICATIONS:

Material: Phosphor Bronze, 0.2mm thick

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 VAC

Current rating: 3 A

Contact resistance: 20 mohms max

Mechanical:

Wire Range: 22-28 AWG.

Packaging: 10K Pcs / Reel

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			DATE		
DRAWN	DY		2/10/10		
CHECKED					
APPROVED					
			TITLE		
			.098 [2.50] CRIMP TERMINAL		
SIZE		PART NO.		REV.	
X		25CTE-R		B	
REF: S00123T			SCALE: NTS		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25CTE-R](#)