



APPROVED: _____

DATE: _____ TITLE: _____




Rev	AWO #	Description	Date	Appr
-		RELEASED	12/17/09	
A		UPDATED 1 & B DIMENSIONS	1/15/15	
B		UPDATE DRAWING	6/7/18	AY/KC




RECOMMENDED PCB LAYOUT



2P



ASSEMBLY VIEW



Positions: 02 thru 20

A = .098 [2.50] x of Spaces

B = .098 [2.50] x of Spaces +.197 [5.00]

C = .098 [2.50] x of Spaces +.138 [3.50]

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Nature

Contacts: Brass, Tin plated

Electrical:

Voltage rating: 250V AC/DC

Current rating: 3A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		HOLES		TITLE	
.X	± .10	Ø.X	± .10	.098 [2.50] SHROUDED HEADER, RIGHT ANGLE	
.XX	± .020	Ø.XX	± .015		
.XXX	± .015	Ø.XXX	± .010		
APPROVALS		DATE		SIZE	
DRAWN	DY	12/17/09		PART NO.	
CHECKED				25SH-B-XX-TR	
APPROVED				REV. B	
REF: S00124T		SCALE: NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25SH-B-17-TR](#) [25SH-B-10-TR](#) [25SH-B-04-TR](#) [25SH-B-12-TR](#) [25SH-B-09-TR](#) [25SH-B-06-TR](#) [25SH-B-07-TR](#)
[25SH-B-02-TR](#) [25SH-B-08-TR](#) [25SH-B-14-TR](#) [25SH-B-15-TR](#) [25SH-B-13-TR](#) [25SH-B-05-TR](#) [25SH-B-11-TR](#) [25SH-](#)
[B-03-TR](#)