







APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		PART REVISION	4/19/06	
B		ADDED DIM.	8/11/09	
C		UPDATE DRAWING	4/13/18	AY/MY



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Contact: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Rated Voltage: 250V AC/DC

Rated Current: 3A AC/DC

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 1000V AC for 1 minute.

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Spaces + .197 [5.00]

C = .098 [2.50] x No. of Spaces + .138 [3.50]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	LFJ	4/13/06
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
WIRE TO BOARD PITCH: 2.5MM WAFER STRAIGHT TYPE W/ KINK			
SIZE X	PART NO. 25SH-B-XX-TS	REV. C	
REF:	S00124T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25SH-B-10-TS](#) [25SH-B-03-TS](#) [25SH-B-08-TS](#) [25SH-B-14-TS](#) [25SH-B-11-TS](#) [25SH-B-07-TS](#) [25SH-B-02-TS](#)
[25SH-B-16-TS](#) [25SH-B-15-TS](#) [25SH-B-13-TS](#) [25SH-B-04-TS](#) [25SH-B-12-TS](#) [25SH-B-09-TS](#) [25SH-B-05-TS](#) [25SH-](#)
[B-06-TS](#)