





Rev	AWO #	Description	Date	Appr
-		RELEASED	04/19/05	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:
 Material:
 Insulator: PBT, glass reinforced, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
Plating:
 Gold Flash over Nickel underplate overall
Electrical:
 Current rating: 1 Amp max
 Contact resistance: 20 mohms max
 Insulation resistance: 5000 Mohms min
Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.

A = .079 [2.00] X No. of Spaces + .362 [9.20]
 B = .079 [2.00] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: 2.0mm BOX HEADER, VERTICAL
 PCB, GOLD PLATED

APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

SIZE	PART NO.	REV.
X	2BHR-XX-VUA	-

REF: SCALE: NTS SHEET 1 OF 1



6 5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2BHR-14-VUA](#) [2BHR-08-VUA](#) [2BHR-12-VUA](#) [2BHR-20-VUA](#) [2BHR-16-VUA](#) [2BHR-10-VUA](#) [2BHR-26-VUA](#) [2BHR-40-VUA](#) [2BHR-30-VUA](#) [2BHR-24-VUA](#) [2BHR-34-VUA](#) [2BHR-06-VUA](#)