





Rev	AWO #	Description	Date	Appr
-		RELEASED	8/11/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 6T, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold Flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 1000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55C to +105C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 265 for 5 sec.



A = .079 [2.00] X No. of Spaces + .362 [9.20]
B = .079 [2.00] X No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

2.0mm BOX HEADER, VERTICAL PCB
GOLD PLATED, HI-TEMP

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES. [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
.X	± .10	ØX	± .10	2.0mm BOX HEADER, VERTICAL PCB			
.XX	± .020	ØXX	± .015	GOLD PLATED, HI-TEMP			
.XXX	± .015	ØXXX	± .010	2BHR-XX-VUA-HT			
APPROVALS				REV.			
DATE				-			
DRAWN	SS	8/11/05					
CHECKED							
APPROVED							

A

B

C

D

A

B

C

D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2BHR-10-VUA-HT](#) [2BHR-14-VUA-HT](#) [2BHR-20-VUA-HT](#) [2BHR-44-VUA-HT](#)