

6

5

4

3



2

1


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/5/03	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Nylon 6T, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold Flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



A = .079 [2.00] X No. of Spaces + .362 [9.20]
B = .079 [2.00] X No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-0214			
.X	± .10	ØXX	± .10	TITLE 2.0 MM BOX HEADER, VERTICAL, GOLD FLASH, SURFACE MOUNT			
.XX	± .020	ØXXX	± .015	DRAWN SLS			
.XXX	± .015	ØXXX	± .010	CHECKED			
APPROVALS				DATE			
DRAWN				11/5/03			
CHECKED				SIZE			
APPROVED				X			
REF:				PART NO.			
SCALE: NTS				2BHR-XX-VUA-SMT			
SHEET 1 OF 1				REV.			
				-			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2BHR-34-VUA-SMT](#) [2BHR-16-VUA-SMT](#) [2BHR-26-VUA-SMT](#) [2BHR-24-VUA-SMT](#) [2BHR-64-VUA-SMT](#) [2BHR-50-VUA-SMT](#) [2BHR-30-VUA-SMT](#) [2BHR-14-VUA-SMT](#) [2BHR-40-VUA-SMT](#) [2BHR-20-VUA-SMT](#) [2BHR-60-VUA-SMT](#) [2BHR-10-VUA-SMT](#) [2BHR-44-VUA-SMT](#) [2BHR-08-VUA-SMT](#)