




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		REDRAWN	11/16/11	
B		REVISED SPEC.	1/8/13	

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



SPECIFICATIONS:

Material:  
Insulator: Nylon 66, rated UL 94V-2  
Insulator color: White  
Electrical:  
Operating voltage: 150 VAC max  
Current rating: 2 Amp max  
Insulation resistance: 1,000 Mohms min @ 500 VDC  
Dielectric withstanding voltage: 800 VAC for 1 minute  
Temperature Rating:  
Operating temperature: -25°C to +85°C  
Environmental:  
Lead free, RoHS compliant

Positions: 2 thru 20  
A = .079 [2.00] x No. of Spaces + .150 [3.80]  
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		HOLES	
.X	± .10	ØX	± .10		
.XX	± .020	ØXX	± .015		
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE			
DRAWN	SS	4/6/05			
CHECKED					
APPROVED					
TITLE		SIZE		PART NO.	
.079 [2.00] CRIMP HOUSING		X		2CH-C-XX	
909 Rahway Avenue, Union, NJ 07083		REF: S00016T		SCALE: NTS	
Phone: 908-687-5000 Fax: 908-687-5710		SHEET 1 OF 1		REV. B	
LOW PROFILE, DUAL POLARIZED					

ADAM TECH

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2CH-C-09](#) [2CH-C-05](#) [2CH-C-03](#) [2CH-C-06](#) [2CH-C-04](#) [2CH-C-02](#) [2CH-C-08](#) [2CH-C-10](#) [2CH-C-07](#)