






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	7440	RELEASED	01/16/07	
A		REVISED SHAPE	9/15/10	
B		REVISED SPEC.	4/20/16	AY/IC



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

30u" Gold over Nickel on contact area,

Tin over copper underplate on IDC area.

Electrical:

Voltage rating: 250 VAC

Current rating: 3 Amp.

Contact resistance: 20 mohms max.

Insulation resistance: 5000 Mohms min.@ DC 500V

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 6 thru 34, 38, 40, 44, 50, 60, 62, 64, 68

A = .079 [2.00] x No. of Positions per Row + .205 [5.20]

B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	BW	01/16/07
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] FLAT CABLE IDC SOCKET

SIZE	PART NO.	REV.
X	2FCS-XX-SG-PB	B
REF: S00087T		SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2FCS-12-SG-PB](#) [2FCS-22-SG-PB](#) [2FCS-44-SG-PB](#) [2FCS-50-SG-PB](#) [2FCS-24-SG-PB](#) [2FCS-14-SG-PB](#) [2FCS-34-SG-PB](#)
[2FCS-06-SG-PB](#) [2FCS-36-SG-PB](#) [2FCS-40-SG-PB](#) [2FCS-60-SG-PB](#) [2FCS-08-SG-PB](#) [2FCS-16-SG-PB](#)
[2FCS-20-SG-PB](#) [2FCS-10-SG-PB](#)