





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/14/09	
A		REVISED DIM.	11/6/13	AY/GC



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min @ 500 VDC
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant



Positions: 2 thru 40
A = .079 [2.00] x No. of Positions
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes		ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 .XX ± .020 .XXX ± .015	Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010	TITLE .079 [2.00] SINGLE ROW PIN HEADER SURFACE MOUNT, TYPE B	
APPROVALS	DATE		
DRAWN	DY	7/14/09	
CHECKED			
APPROVED			
SIZE	PART NO.	2PH1-XX-UA-SMT-B	REV. A
REF: S00039T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2PH1-18-UA-SMT-B](#) [2PH1-06-UA-SMT-B](#) [2PH1-08-UA-SMT-B](#) [2PH1-04-UA-SMT-B](#) [2PH1-12-UA-SMT-B](#) [2PH1-14-](#)
[UA-SMT-B](#) [2PH1-40-UA-SMT-B](#) [2PH1-02-UA-SMT-B](#) [2PH1-16-UA-SMT-B](#) [2PH1-10-UA-SMT-B](#) [2PH1-20-UA-SMT-B](#)