





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/31/05	
A		REVISED DIM.	1/9/14	AY/TTW



SPECIFICATIONS:

Material:
Insulator: PBT, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min @ 500 VDC
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant

Positions: 4 thru 80
A = .079 [2.00] x No. of Positions per Row
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		HOLES	
.X	± .10	ØX	± .10		
.XX	± .020	ØXX	± .015		
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE			
DRAWN	SS	3/31/05			
CHECKED					
APPROVED					
TITLE		SIZE		PART NO.	
.079 [2.00] DUAL ROW PIN HEADER		X		2PH2-XX-UA	
GOLD PLATED		REF: S00039T		SCALE: NTS	
				SHEET 1 OF 1	
				REV. A	

A

B

C

D

A

B

C

D

6

5

5

4

3

2

1

4

3

2

1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2PH2-18-UA](#) [2PH2-02-UA](#) [2PH2-08-UA](#) [2PH2-06-UA](#) [2PH2-20-UA](#) [2PH2-10-UA](#) [2PH2-12-UA](#) [2PH2-04-UA](#)
[2PH2-14-UA](#) [2PH2-16-UA](#)